
FISHER & PAYKEL

DATA SHEET

Combination Steam Oven, 24"



Model no: OS24SDTDX2

(refer page 2 for metric measurements)

Product Dimensions	in
 Ø Overall height of oven 	18"
Overall width of oven	23 7/16"
© Overall depth of oven (excludes handle and front metal trim)	22 1/4"
 Depth of oven frame, control panel and door (excludes handle and front metal trim) 	13/16"
© Depth of chassis	21 7/16"
F Height of chassis	17 1/8"
© Width of chassis	21 7/8"
 Height from bottom datum to top of oven door 	13 11/16"
 Height of control panel 	3 15/16"
④ Height of metal cap on control panel	13/16"
® Height from bottom datum to centerline of handle	12 3/4"
() Width of handle	22 1/4"
Ø Depth of handle (measured from front of door)	15/8"
8 Thickness of handle	5/8"
O Distance from bottom datum to bottom of door glass	1/2"
P Depth of door when open (measured from front of door)	12 5/8"
③ Control panel fully open (measured from front of door)	6 11/16"
R Control panel half open (measured from front of chassis)	3 5/16"
S Water tank carriage fully open	5 1/4"
Minimum Clearances	in
Minimum inside height of cavity	17 5/16"
Minimum inside width of cavity	22 1/16"
Minimum inside depth of cavity	21 5/8"

Minimum inside depth of cavity	21 5/8"
Overall height of cabinetry (cavity around front frame)	18 1/8"
Overall width of cabinetry (cavity around front frame)	23 5/8"
Rear ventilation air vent depth*	2"
Rear ventilation air vent width*	22 1/16"

* A rear ventilation air vent totalling 44in2 (280cm2) is required. The air vent must be located at the rear of the cabinet, it can be positioned at the base, sides, back or top of the cavity.

IMPORTANT NOTE: For full installation and clearance details please refer to the installation guide.

INDICATES PRODUCT DATUM -------

DATE: 17.10.2022

IMPORTANT NOTE: Throughout this guide, dimensions may vary by ±2mm (1/16"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com

FISHER & PAYKEL

DATA SHEET

mm

458

596

565

20

545 435

556 347

100 20

324

565

42

16 12

320

170



Model no: OS24SDTDX2

G 0 ß чћг. G Ø ß Ø Ø PLAN VIEW Ø **B** 596 **G** 545 ۵ Ο Ø h. 0 **A** 458 Ø ٠ ß DATUM : BOTTOM OF CHASSIS 0 FRONT VIEW **PROFILE VIEW** Ø

400

Millimetres

(refer page 1 for imperial measurements) **Product Dimensions** A Overall height of oven Overall width of oven © Overall depth of oven (excludes handle and front metal trim) (b) Depth of oven frame, control panel and door (excludes handle and front metal trim) (E) Depth of chassis Height of chassis
 Width of chassis (Height from bottom datum to top of oven door ① Height of control panel ④ Height of metal cap on control panel (8) Height from bottom datum to centerline of handle (L) Width of handle (Depth of handle (measured from front of door)

Distance from bottom datum to bottom of door glass
 Depth of door when open (measured from front of door)

③ Control panel fully open (measured from front of door)

® Control panel half open (measured from front of chassis)	84
Water tank carriage fully open	133
Minimum Clearances	mm
Minimum inside height of cavity	440
Minimum inside width of cavity	560
Minimum inside depth of cavity	550
Overall height of cabinetry (cavity around front frame)	460
Overall width of cabinetry (cavity around front frame)	600
Rear ventilation air vent depth*	50
Rear ventilation air vent width*	560

* A rear ventilation air vent totalling 44in2 (280cm2) is required. The air vent must be located at the rear of the cabinet, it can be positioned at the base, sides, back or top of the cavity.

IMPORTANT NOTE: For full installation and clearance details please refer to the installation guide.

DATE: 17.10.2022

(N) Thickness of handle

IMPORTANT NOTE: Throughout this guide, dimensions may vary by $\pm 2mm$ (1/16"). Please read the installation manual for detailed information on installing the product. For full installation instructions & specifications visit fisherpaykel.com